


Nunc™ Cell Factory® culture chambers

Intensive cell culture unit consisting of superimposed trays of transparent polystyrene treated for culture.

- Ideal for scale up
- Space and time saving
- Parallel culture chambers communicating over the height by 2 vertical ducts, one equipped with a hydrophobic 0.2 µm filter for aeration, the other for filling and emptying in aseptic condition
- Equal distribution per chamber according to the principle of communicating vessels
- Nunclon surface treatment, gamma sterilised, individually wrapped
- Harvesting of cells by trypsinisation
- Drainage through a connecting tube
- Dimensions L x W : 335 x 205 mm



Accessories for Cell Factory® standard

Cat. No.	Description	Units/ carton	€ Excl. VAT/ carton
056780	HDPE closure caps	40	NC -
055132	PTFE connection fitting (for draining and filling)	10	NC -
056420	Polycarbonate fitting	10	NC -
055469	1 µm vent filter	1	NC -

Cell Factory® standard

Cat.No.	Surface area (cm²)	Number of trays	Working volume (ml)	H. (mm)	Units/ bag	Units/ carton	€ Excl. VAT/ carton
055124	632	1	180	37	1	8	NC -
055125	1264	2	360	52	1	6	NC -
056194	2528	4	720	90	1	10	NC -
055126	6320	10	1800	190	1	2	NC -
055127	6320	10	1800	190	1	6	NC -
055128	25280	40	7200	695	1	2	NC -

Cell Factory® EasyFill®

- Space saving
- One Cell factory Easy fill 10 trays corresponds to 36 T175 vials
- Easy to fill and empty, ready to use, no accessories needed
- Dimensions L x W : 335 x 205 mm

Cat.No.	Surface area (cm²)	Number of trays	Working volume (ml)	H. (mm)	Units/ bag	Units/ carton	€ Excl. VAT/ carton
056440	630	1	200	35	1	6	NC -
056442	1260	2	400	53	1	6	NC -
056443	2520	4	800	87	1	4	NC -
056705	6300	10	2000	190	1	2	NC -

Accessory for Cell Factory EasyFill™

Cat. No.	Description	Units/ carton	€ Excl. VAT/ carton
056420	Polycarbonate fitting	40	NC -



High density Cell Factory



High density Cell Factory®

- 30% more surface area and output within the standard footprint of the Nunc™ Cell Factory® system
- Yields may vary depending on the cell type being grown
- Productivity improvement
- Dimensions L x W : 335 x 205 mm

Cat.No.	Surface area (cm²)	Number of trays	Working volume (ml)	H. (mm)	Units/ bag	Units/ carton	€ Excl. VAT/ carton
056903	1896	3	450-600	54	1	4	NC -
056904	8216	13	1950-2600	186	1	3	NC -
056905	32864	52	7800-10400	698	1	1	NC -



Cell Factory® with active gassing

- Creates an ideal environment for the cultivation of pH sensitive and oxygen consuming cells
- Ensures a controlled and uncontaminated atmosphere on each tray
- Homogeneous distribution of the user-specified gas mixture

Cat.No.	Surface area (cm²)	Number of trays	Working volume (ml)	H. (mm)	Units/ bag	Units/ carton	€ Excl. VAT/ carton
056179	2400	4	600-800	90	1	10	NC -
056180	6000	10	1500-2000	190	1	6	NC -
056181	24000	40	6000-8000	695	1	2	NC -