

Films for Fluorescence

ClearLine

ClearLine® AbsorbMax® and BrightMax® Films



Enter the Cat. No. on Dulis.nl to find the complete Excel film guide

Applications: luorescence, luminescence.

- ▶ In 203.2 µm vinyl
- ▶ Operating temperature : -40 °C to 80 °C
- ▶ Without tab
- ▶ Opaque
- ▶ AbsorbMax: absorbs light, reduces stray light
- ▶ BrightMax: reflects light and increases sensitivity

Cat. No.	Description	Dimensions (mm)	Units/ carton	€ Excl. VAT/ carton
760241	ClearLine® AbsorbMax® Film for black plate	114.3 x 76.2	100	NC -
760245	ClearLine® BrightMax® Film for white plate	116.1 x 76.2	100	NC -

Thermo SCIENTIFIC | **nunc**

Nunc adhesive films




- ▶ Can be used from -40 °C to +80 °C

Cat. No.	DNase RNase free	Applications	Drillable	Colour	Material	Units/ carton	€ Excl. VAT/ carton
056110	Yes	To be drilled, low autofluorescence	Yes	Transparent	Polyethylene	100	NC -
056486	No	Opaque film for photosensitive material	No	Black	Vinyl	50	NC -
056889	No	Luminescence	No	White	Polyester	50	NC -

Aluminium films

ClearLine

ClearLine® AlumaSeal II® Film



DNase RNase


Applications : PCR, long-term storage

- ▶ 35.6 µm aluminium
- ▶ Operating temperature : -80°C to +120 °C
- ▶ Universal
- ▶ Dimensions without tab: 125.4 x 82.6 mm
- ▶ With two detachable tabs
- ▶ Good chemical resistance
- ▶ Drillable
- ▶ Opaque
- ▶ Does not withdraw into itself

Cat. No.	Description	Units/ carton	€ Excl. VAT/ carton
760212	ClearLine® AlumaSeal II® Film	100	NC -
760213	ClearLine® AlumaSeal II® Film, sterile	50	NC -
765248	ClearLine® AlumaSeal II® Film in 100 m rolls	1	NC -

ClearLine

ClearLine® AlumaSeal 96® and AlumaSeal 384® Films



DNase RNase

Applications : PCR, long-term storage

- ▶ 38.1 µm aluminium
- ▶ Operating temperature : -80 °C to +120 °C
- ▶ With a tab
- ▶ Drillable
- ▶ Opaque
- ▶ Reinforced sealing for 96-well plates

Cat.No	Description	Dimensions (mm)	Units/ carton	€ Excl. VAT/ carton
760231	ClearLine® AlumaSeal 96® Film for 96-well plate, non-skirted	117.5 x 77.8	100	NC -
760232	ClearLine® AlumaSeal 384® Film for 384-well plate or Deepwell	123.8 x 82.6	100	NC -